

# 02 MiniT Series Mini-Dry Bath Incubator

## Features

1. LCD display. It is easy to set and use
2. Small footprint: MiniT series are a personal sized that fits in the palm on your hand
3. Simultaneous display actual time, temperature
4. Temperature deflection adjusting meet with different demands
5. Beep-signal/Stop after program completed
6. With DC12V or DC24V power for total portability, beep-signal/stop after program completed
7. Interchangeable aluminum alloy sample blocks provide versatility and allow easy cleaning and disinfecting



MinT

MiniT-C

MiniT-100

MiniT-100H

## Specification

Model	MiniT	MiniT-C	MiniT-100	MiniT-100H
Temperature control range	RT.+5-80°C	0°C-100°C	RT.+5°C-100°C	RT.+5°C-100°C
Timer range	1-999min or 1-999sec	1-999min or 1-999sec	1-999min or 1-999sec	1-999min or 1-999sec
Temp. control accuracy	±0.5°C	±0.5°C	±0.5°C	±0.5°C
Display accuracy	±0.1°C	±0.1°C	±0.1°C	±0.1°C
Heating time (25°C to Max.)	≤12min	≤20min	≤15min	≤15min
Cooling time (25°C to 0°C)	—	≤25min	—	—
Temp. control accuracy	±0.3°C	±0.3°C	±0.3°C	±0.3°C
Heating Lid	—	—	—	Heating Lid
Lid's temperature range	—	—	—	RT.+5°C-100°C
Dimensions (W x D x H)mm	150 × 110 × 100 mm	162 × 110 × 140 mm	152 × 120 × 112 mm	152 × 120 × 112 mm
Weight	0.5kg	1.0kg	0.8kg	0.9kg
Power supply	DC 12V	DC 12V	DC 24V	DC 24V

# 03 MiniT-H2C/MiniT-H3 Mini-Dry Bath Incubator

## Features

1. Working area dimension: 3 individual controller
2. LCD display. It is easy to set and use
3. Simultaneously display the set and actual time, temperature, Auto-stop and sound-alert after program completed
4. Temperature deflection adjusting meet different demands
5. MiniT-H3 has a heating function only and its temperature ranges from RT.+5~100°C
6. MiniT-H2C has cooling/heating function and its temperature ranges from 0°C~99.9°C



MiniT-H2C/MiniT-H3

## Specification

Model	MiniT-H3			MiniT-H2C		
	Block - A	Block - B	Block - C	Block - A	Block - B	Block - C
Working area	Block - A	Block - B	Block - C	Block - A	Block - B	Block - C
Temperature Control Range	RT.+5~99.9°C	RT.+5~99.9°C	RT.+5~99.9°C	0~99.9°C	RT.+5~99.9°C	RT.+5~99.9°C
Heating time (25°C to 99.9°C)	≤20min	≤20min	≤20min	≤20min	≤20min	≤20min
Cooling time (25°C to 99.9°C)	--	--	--	≤25min (*)	--	--
Temp. control accuracy	≤0.5°C			≤0.5°C		
Temp. stability @37°C	0.2°C			0.2°C		
Display accuracy	0.1°C			0.1°C		
Timer range	1~ 999h or 1~ 999min or 1~ 999sec			1~999h or 1~999min or 1~999sec		
Block quantity	3			3		
Power supply	DC12V,120W			DC12V,120W		
Dimensions (mm)	360×180×150			360×180×150		
Weight	3kg			3kg		

\*1. Tested in ambient temperature <25°C

## Ordering information

No.	Code	Description
01	AS-01130-00	MiniT mini dry bath, DC12V, 40w
02	AS-01170-00	MiniT-C mini dry bath, DC12V, 60w
03	AS-01150-00	MiniT-100 mini dry bath, DC24V, 40w
04	AS-01160-00	MiniT-100H mini dry bath, DC24V, 50w
05	AS-01220-00	MiniT-H3 3-in-1 mini dry bath
06	AS-01230-00	MiniT-H2C 3-in-1 mini dry bath

## Accessories

No.	Code	Type	Description
01	AS-01131-01	A-MinT	40×0.2ml tubes
02	AS-01131-02	B-MinT	24×0.5ml tubes
03	AS-01131-03	C-MinT	15×1.5ml tubes
04	AS-01131-04	D-MinT	15×2.0ml tubes
05	AS-01131-05	E-MinT	8×12.5×12.5ml cuvette block
06	AS-01131-06	F-MinT	4×15ml tubes
07	AS-01131-07	G-MinT	2×50ml tubes
08	AS-01131-99	Can be customized according to customer demand	

Note: MiniT-100H can just use A-MiniT block and can not exchange!

### MiniT series and MiniT-H2C/MiniT-H3 blocks

